


Operation, Installation and Maintenance Manual

DK-MH 30/T plus-SWF MED


2-way horn speaker for marine application, 30W power,
certified MED/1.44b



Technical Data

Colour	RAL 7035
Dimensions	370x255x291 mm
Dispersion -6dB, 500Hz	140°/194° h/v
Dispersion -6dB, 1KHz	70°/105° h/v
Dispersion -6dB, 2KHz	51°/109° h/v
Dispersion -6dB, 4KHz	46°/120° h/v
Frequency Range	95 - 22.000 Hz
Frequency Response	80 - 24.000 Hz
Power	30/15/7,5/3,75 W

Environmental Category: Category B (IEC 60945 - Exposed Equipment)



(EU) 2025/1533, item No. MED/1.44b. SOLAS 1974 as
amended, Regulation II-2/12,21,22, III/4, 6 & X/3, LSA Code VII,
HSC Code 4,8, IMO MSC.1/Circ. 808, 1369/Add.1
suitable for:

- Cargo ships
- Passenger ships without SRtP
- Passenger ships with SRtP

Compass Safe Distance: min. 5 m
to prevent magnetic interference with navigational instruments

TO MAKE PEOPLE LISTEN



DK-MH 30/T PLUS-SWF MED

Mounting Instruction

1. Mount the U-bracket on the ceiling with the appropriate screws for the surface.
2. If necessary, remove the speaker enclosure from the U-bracket.
3. Insert the loudspeaker cable through the cable entry of the previously removed rear wall of the housing.
4. Connect the loudspeaker cable to the terminals 100V and COM.
If necessary, select a different power tapping.
5. Carefully reinsert the back panel into the housing.



CE-Symbol according to 93/68EWG
Measurements according to DIN IEC 268-5
RoHS compliant (2011/65/EU)

ic audio GmbH, Boehringerstraße 14A
68307 Mannheim, Germany

MED certification
Notified
Body No.: 0098
Certificate No.:
MEDB0000AMS